




# R-Series Dia-Vac - R224 (50 Hz)



<b>Max Pressure =</b>	70.0 PSIG (4.80 barG) <b>Parallel</b>
	75.0 PSIG (5.17 barG) <b>Series</b>
	75.0 PSIG (5.17 barG) <b>Series/Parallel</b>
<b>Max Vacuum =</b>	24.8 InHg (839 mBarG) <b>Parallel</b>
	29.4 InHg (995 mBarG) <b>Series</b>
	28.6 InHg (968 mBarG) <b>Series/Parallel</b>
<b>Max Flow =</b>	83.0 LPM (2.93 CFM) <b>Parallel</b>
	23.0 LPM (0.81 CFM) <b>Series</b>
	44.6 LPM (1.57 CFM) <b>Series/Parallel</b>

-Test results are averaged, and therefore should be considered approximate.  
-Tests performed with 316ss head, Teflon® diaphragm, 1/4 inch diameter hose x 5 ft. line at 75° F, using a std. 1430 rpm motor at 50 Hz.  
-These test results are for reference only, and are intended to help provide information to the user when determining which pump to buy. Actual pump performance will depend upon the users' applications.  
**-For 60 Hz operation, increase output by 20%.**