




R-Series Dia-Vac - R254 (50 Hz)



Max Pressure =	75.0 PSIG (5.1 barG) Parallel 75.0 PSIG (5.1 barG) Series 75.0 PSIG (5.1 barG) Series/Parallel
Max Vacuum =	24.9 InHg (843 mBarG) Parallel 29.8 InHg (1009 mBarG) Series 29.1 InHg (985 mBarG) Series/Parallel
Max Flow =	89.6 LPM (3.15 CFM) Parallel 26.1 LPM (0.91 CFM) Series 47.4 LPM (1.66 CFM) Series/Parallel

-Test results are averaged, and therefore should be considered approximate.
-Tests performed with 316ss head, Teflon® diaphragm, 1/4 inch diameter hose x 5 ft. line at 75° F, using a std. 1430 rpm motor at 50 Hz.
-These test results are for reference only, and are intended to help provide information to the user when determining which pump to buy. Actual pump performance will depend upon the users' applications.
-For 60 Hz operation, increase output by 20%.