




# R-Series Dia-Vac - R254 (60 Hz)



<b>Max Pressure =</b>	5.1 bar gauge <b>Parallel</b>
	5.1 bar gauge <b>Series/Parallel</b>
<b>Max Vacuum =</b>	170 mbar abs. <b>Parallel</b>
	4 mbar abs. <b>Series</b>
	28 mbar abs. <b>Series/Parallel</b>
<b>Max Flow =</b>	108 LPM <b>Parallel</b>
	31.4 LPM <b>Series</b>
	57.1 LPM <b>Series/Parallel</b>

-Test results are averaged, and therefore should be considered approximate.  
-Tests performed with 316ss head, Teflon® diaphragm, 1/4 inch (6.35 mm) diameter hose x 1.5 m line at 23.9° C, using a std. 1750 rpm motor at 60 hertz.  
-These test results are for reference only, and are intended to help provide information to the user when determining which pump to buy. Actual pump performance will depend upon the users' applications.  
-For 50 Hz operation, reduce output by 17%.