




# H-Series Dia-Vac - H302 (50 Hz)



**Max Pressure** = 4.14 bar gauge **Parallel**  
4.14 bar gauge **Series**  
**Max Vacuum** = 96 mbar abs. **Parallel**  
14 mbar abs. **Series**  
**Max Flow** = 69.1 SLPM **Parallel**  
36.0 SLPM **Series**

-Test results are averaged, and therefore should be considered approximate.  
-Tests performed with 316ss head, Teflon® diaphragm, 1/4 inch (6.35 mm) diameter hose x 1.5 m line at 23.9° C, using a std. 1725 rpm motor.  
-These test results are for reference only, and are intended to help provide information to the user when determining which pump to buy. Actual pump performance will depend upon the users' applications.  
-For 60 Hz operation, increase output by 20%.