




# R-Series Dia-Vac - R254 (60 Hz)



<b>Max Pressure =</b>	5.1 bar gauge <b>Parallel</b>
	5.1 bar gauge <b>Series/Parallel</b>
<b>Max Vacuum =</b>	170 mbar abs. <b>Parallel</b>
	4 mbar abs. <b>Series</b>
	28 mbar abs. <b>Series/Parallel</b>
<b>Max Flow =</b>	108 LPM <b>Parallel</b>
	31.4 LPM <b>Series</b>
	57.1 LPM <b>Series/Parallel</b>

-Test results are averaged, and therefore should be considered approximate.  
-These test results are for reference only, and are intended to help provide information to the user when determining which pump to buy. Actual pump performance will depend upon the users' applications.  
-For 50 Hz operation, reduce output by 17%.